

Specifications

Product Description :Methanol ER 25L
Product Code :Q3240C

Sr.No	Description	Unit	Standards
1	Description : Clear colorless liquid (< 10 Hazen) (characteristic Odor)		Should Comply
2	Oxidising Substances : Passes test		Should Comply
3	Solubility : Miscible with water forming clear colorless solution		Should Comply
4	Acidity (as HCOOH)	%	0.001 Max
5	Aldehydes & Ketones [(CH ₃) ₂ CO] (by G.C.)	%	0.005 Max
6	Alkalinity (NH ₃)	%	0.0003 Max
7	Assay (by G.C.)	%	99.5 Min
8	Chloride (Cl)	PPM	0.5 Max
9	Cobalt (Co)	PPM	0.05 Max
10	Copper (Cu)	PPM	0.01 Max
11	Ethanol (by G.C.)	%	0.1 Max
12	Manganese (Mn)	PPM	0.01 Max
13	Nickel (Ni)	PPM	0.05 Max
14	Non-volatile matter	%	0.001 Max
15	Refractive Index at 20°C		1.328 - 1.33
16	Substance reducing permanganate (O)	%	0.00025 Max
17	Water (by K.F.)	%	0.1 Max
18	Weight per ml (at 20°C) (In gm/ml)		0.79 - 0.792
19	Zinc (Zn)	PPM	0.01 Max

Specifications

Product Description :Methanol ER 25L
Product Code :Q3240C

Quality Assurance

The document has been produced electronically and is valid without signature.

Registered Office : Thermo Fisher Scientific India Pvt. Ltd. 403-404,B-wing, Delphi, Hiranandani Business Park, Powai, Mumbai-400076, INDIA.
Tel : +91-22-67162200/66803000, CIN-U73100MH2000PTC126872.