


CATALOG NO.	NOMINAL CAPACITY, (oz)							MATERIALS		
	BOTTLE				CLOSURE					
322020	1	2	4	8	16	16	32	64	PETG	HDPE

SIZE CODE.....	-0030		-0060		-0125		-0250	
SIZE (NOM VOL mL/oz)	30/1		60/2		125/4		250/8	
NOM. BRIM CAP. (mL)	45		77		175		320	
NECK FINISH (mm)....	20-415		24-415		38-430		38-430	
THREAD (T.P.I.)....	8		8		6		6	
NOM. WEIGHT W/CLOSURE (gms)....	14.5		22		52.5		65	
	INCHES	MM	INCHES	MM	INCHES	MM	INCHES	MM
A (BTLE. NECK I.D.):	0.54±.02	13.7±.5	0.70±.02	17.8±.5	1.100±.025	27.94±.64	1.100±.025	27.94±.64
B (HT. W/CLOSURE)...	2.50±.05	63.5±1.3	3.25±.06	82.6±1.5	4.26±.08	108.2±2.0	5.70±.08	144.8±2.0
C (HT. W/O CLOSURE):	2.39±.05	60.7±1.3	3.15±.06	80.0±1.5	4.08±.08	103.6±2.0	5.50±.08	139.7±2.0
D (SQUARE).....	1.50±.05	38.1±1.3	1.58±.05	40.1±1.3	2.06±.06	52.3±1.5	2.32±.06	58.9±1.5
MIN. WALL @ BTM COR.:	0.006	0.15	0.006	0.15	0.008	0.20	.009	0.23
MIN. WALL ELSEWHERE:	0.008	0.20	0.010	0.25	0.012	0.30	0.016	0.41
MIN. WALL @ HANDLE COR:	-	-	-	-	-	-	-	-

SIZE CODE.....	-0500		-9500		-1000		-2000	
SIZE (NOM VOL mL/oz)	500/16		500/16		1000/32		2000/64	
NOM. BRIM CAP. (mL)	610		658		1225		2380	
NECK FINISH (mm)....	38-430		38-430		38-430		53B	
THREAD (T.P.I.)....	6		6		6		4	
NOM. WEIGHT W/CLOSURE (gms)....	116		116		187		350	
	INCHES	MM	INCHES	MM	INCHES	MM	INCHES	MM
A (BTLE. NECK I.D.):	1.100±.025	27.94±.64	1.100±.025	27.94±.64	1.100±.025	27.94±.64	1.53±.03	38.9±.8
B (HT. W/CLOSURE)...	7.00±.09	177.8±2.3	7.00±.09	177.8±2.3	8.63±.10	219.2±2.5	10.65±.14	270.5±3.6
C (HT. W/O CLOSURE):	6.82±.09	173.2±2.3	6.82±.09	173.2±2.3	8.48±.10	215.49±2.5	10.42±.14	264.7±3.6
D (SQUARE).....	2.88±.06	73.2±1.5	3.00±.06	76.2±1.5	3.63±.07	92.2±1.8	4.55±.09	115.6±2.3
MIN. WALL @ BTM COR.:	0.014	0.36	0.014	0.36	0.014	0.36	0.020	0.51
MIN. WALL ELSEWHERE:	0.020	0.51	0.017	0.43	0.020	0.51	0.020	0.51
MIN. WALL @ HANDLE COR:	-	-	-	-	-	-	0.008	0.20

NOTES:

1. ALL DIMENSIONS ARE NOMINAL AND IN INCHES AND MILLIMETERS UNLESS OTHERWISE NOTED.
2. THIS IS NOT A PRODUCTION DRAWING, BUT IS FOR INFORMATIONAL PURPOSES ONLY, AND IS SUBJECT TO CHANGE WITHOUT NOTICE.



SPECS ON BACK

NOT TO SCALE

CONFIDENTIAL

THIS PRODUCT SPECIFICATION SHEET CONTAINS CONFIDENTIAL AND/OR PROPRIETORY INFORMATION AND IS TO BE USED ONLY FOR THE EXPRESSED PURPOSES AGREED UPON BY AN AUTHORIZED OFFICER OF THERMO FISHER SCIENTIFIC.

ThermoFisher
SCIENTIFIC

 Thermo Fisher Scientific
 75 Panorama Creek Drive
 Rochester, NY 14625-2385, USA

MADE	JDC	APP'D	PWC
CK'D	KOW	3/9/15	
DESCRIPTION:			PSS 32-2020-XXXX

PETG SQUARE MEDIA BOTTLES