

SAFETY DATA SHEET

Creation Date 02-Apr-2009

Revision Date 21-Dec-2025

Revision Number 4

This safety data sheet was created pursuant to the requirements of: US OSHA Hazard Communication Standard 2024 (29 CFR 1910.1200)

1. Identification

Product Name Decahydronaphthalene

Cat No. : A13883

CAS No 91-17-8
Synonyms Bicyclo(4.4.0)decane; Decalin; Naphthalane

Recommended Use Laboratory chemicals.
Uses advised against Food, drug, pesticide or biocidal product use.

Details of the supplier of the safety data sheet

Company

Thermo Fisher Scientific Chemicals, Inc.
30 Bond Street
Ward Hill, MA 01835-8099
Tel: 800-343-0660
Fax: 800-322-4757

Emergency Telephone Number

For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99
CHEMTREC Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

2. Hazard(s) identification

Classification

This chemical is considered hazardous according to [US] OSHA (29 CFR 1910.1200, 2024)

Flammable liquids	Category 3
Acute Inhalation Toxicity - Vapors	Category 3
Skin Corrosion/Irritation	Category 1 C
Serious Eye Damage/Eye Irritation	Category 1
Specific target organ toxicity (single exposure)	Category 3
Target Organs - Respiratory system.	
Aspiration Toxicity	Category 1

Label Elements

Signal Word
Danger

Hazard Statements

Flammable liquid and vapor
May be fatal if swallowed and enters airways
Causes severe skin burns and eye damage
May cause respiratory irritation
Toxic if inhaled

**Precautionary Statements****Prevention**

Use only outdoors or in a well-ventilated area
Do not breathe dust/fume/gas/mist/vapors/spray
Wash face, hands and any exposed skin thoroughly after handling
Wear protective gloves/protective clothing/eye protection/face protection
Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking
Keep container tightly closed
Ground and bond container and receiving equipment
Use explosion-proof electrical/ventilating/lighting equipment
Keep cool
Take action to prevent static discharges
Use non-sparking tools

Response

Immediately call a POISON CENTER or doctor

Inhalation

IF INHALED: Remove person to fresh air and keep comfortable for breathing

Skin

IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower
Take off contaminated clothing and wash before reuse

Eyes

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing

Ingestion

Do NOT induce vomiting

Rinse mouth

Fire

In case of fire: Use CO₂, dry chemical, or foam to extinguish

Storage

Store locked up

Store in a well-ventilated place. Keep container tightly closed

Disposal

Dispose of contents/container to an approved waste disposal plant

Hazards not otherwise classified (HNOC)

Very toxic to aquatic life with long lasting effects

Hazards classified under paragraph (d)(1)(ii) of 1910.1200**Hazards resulting from a reaction with other chemicals under normal conditions of use**

May form explosive peroxides.

3. Composition/information on Ingredients

Component	CAS No	Weight %
Decahydronaphthalene	91-17-8	>95

4. First-aid measures

General Advice	Show this safety data sheet to the doctor in attendance. Immediate medical attention is required.
Eye Contact	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Immediate medical attention is required.
Skin Contact	Wash off immediately with plenty of water for at least 15 minutes. Immediate medical attention is required.
Inhalation	If not breathing, give artificial respiration. Do not use mouth-to-mouth method if victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. Remove to fresh air. Immediate medical attention is required. Risk of serious damage to the lungs (by aspiration).
Ingestion	Do NOT induce vomiting. Call a physician or poison control center immediately. If vomiting occurs naturally, have victim lean forward.
Most important symptoms and effects	Causes burns by all exposure routes. Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting: Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation
Notes to Physician	Treat symptomatically

5. Fire-fighting measures

Suitable Extinguishing Media	Water mist may be used to cool closed containers. CO ₂ , dry chemical, dry sand, alcohol-resistant foam.
Unsuitable Extinguishing Media	No information available
Flash Point	58 °C / 136.4 °F
Method -	No information available
Autoignition Temperature	250 °C / 482 °F
Explosion Limits	
Upper	4.9 vol %
Lower	0.7 vol %
Sensitivity to Mechanical Impact	No information available
Sensitivity to Static Discharge	No information available

Specific Hazards Arising from the Chemical

Thermal decomposition can lead to release of irritating gases and vapors. The product causes burns of eyes, skin and mucous membranes. Flammable. Containers may explode when heated. Vapors may form explosive mixtures with air. Vapors may travel to source of ignition and flash back. Do not allow run-off from fire-fighting to enter drains or water courses.

Hazardous Combustion Products

Carbon monoxide (CO). Carbon dioxide (CO₂).

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

NFPA

Health
3

Flammability
2

Instability
1

Physical hazards
N/A

6. Accidental release measures

Personal Precautions

Ensure adequate ventilation. Use personal protective equipment as required. Evacuate personnel to safe areas. Keep people away from and upwind of spill/leak. Remove all sources of ignition. Take precautionary measures against static discharges.

Environmental Precautions

Do not flush into surface water or sanitary sewer system. Do not allow material to contaminate ground water system. Prevent product from entering drains. Local authorities should be advised if significant spillages cannot be contained.

Methods for Containment and Clean Up

Soak up with inert absorbent material. Keep in suitable, closed containers for disposal. Remove all sources of ignition. Use spark-proof tools and explosion-proof equipment.

7. Handling and Storage

Handling

Do not get in eyes, on skin, or on clothing. Wear personal protective equipment/face protection. Use only under a chemical fume hood. Do not breathe mist/vapors/spray. Do not ingest. If swallowed then seek immediate medical assistance. Keep away from open flames, hot surfaces and sources of ignition. Use only non-sparking tools. Take precautionary measures against static discharges.

Storage.

Keep containers tightly closed in a dry, cool and well-ventilated place. Keep under nitrogen. Keep away from open flames, hot surfaces and sources of ignition. Flammables area. May form explosive peroxides. Containers should be dated when opened and tested periodically for the presence of peroxides. Should crystals form in a peroxidizable liquid, peroxidation may have occurred and the product should be considered extremely dangerous. In this instance, the container should only be opened remotely by professionals. Keep away from heat, sparks and flame. Corrosives area. Store under an inert atmosphere. Air sensitive. Incompatible Materials. Strong oxidizing agents.

8. Exposure controls / personal protection

Exposure Guidelines

This product does not contain any hazardous materials with occupational exposure limit established by the region specific regulatory bodies.

Engineering Measures

Use only under a chemical fume hood. Use explosion-proof electrical/ventilating/lighting equipment. Ensure that eyewash stations and safety showers are close to the workstation location. Ensure adequate ventilation, especially in confined areas.

Personal Protective Equipment**Eye/face Protection**

Wear appropriate protective eyeglasses or chemical safety goggles as described by OSHA's eye and face protection regulations in 29 CFR 1910.133 or European Standard EN166.

Skin and body protection

Wear appropriate protective gloves and clothing to prevent skin exposure.

Respiratory Protection

Follow the OSHA respirator regulations found in 29 CFR 1910.134 or European Standard EN 149. Use a NIOSH/MSHA or European Standard EN 149 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.

Recommended Filter type:

Organic gases and vapours filter. Type A. Brown. conforming to EN14387.

Hygiene Measures

Handle in accordance with good industrial hygiene and safety practice.

9. Physical and chemical properties

Appearance

Physical State

Color

Odor

Odor Threshold

Property

Melting Point/Range

Softening Point

Boiling Point/Range

Flash Point

Flammability (liquid)

Flammability (solid,gas)

Explosion Limits

Autoignition Temperature

Decomposition Temperature

pH

Viscosity

Water Solubility

Solubility in other solvents

Partition Coefficient (n-octanol/water)

Component

Decahydronaphthalene

Vapor Pressure

Density / Specific Gravity

Bulk Density

Vapor Density

Particle characteristics

Liquid

Colorless

Petroleum distillates

No information available

Values

-31 °C / -23.8 °F

No data available

187 °C / 368.6 °F

58 °C / 136.4 °F

Flammable

Not applicable

Lower 0.7 vol%**Upper** 4.9 vol%

250 °C / 482 °F

No data available

7

3 mPa s at 20 °C

Insoluble

No information available

log Pow

4.79

1.3 mbar @ 22 °C

0.882

Not applicable

4.8

Not applicable (liquid)

Remarks• Method

@ 760 mmHg

Method - No information available

On basis of test data

Liquid

Liquid
(Air = 1.0)Other Information

Molecular Formula

Molecular Weight

Explosive Properties

Evaporation Rate

C10 H18

138.25

explosive air/vapour mixtures possible

No information available

10. Stability and reactivity

Reactive Hazard

Yes

Stability

May form explosive peroxides. Hygroscopic. Air sensitive.

Conditions to Avoid

Incompatible products. Keep away from open flames, hot surfaces and sources of ignition.
Excess heat. Exposure to air. Exposure to moisture. Exposure to moist air or water.

Incompatible Materials

Strong oxidizing agents

Hazardous Decomposition Products

Carbon monoxide (CO), Carbon dioxide (CO₂)

Hazardous Polymerization

Hazardous polymerization does not occur.

Hazardous Reactions

None under normal processing.

11. Toxicological information

Information on expected route of exposure

Inhalation	Harmful by inhalation. Irritating to respiratory system.
Ingestion	Aspiration hazard if swallowed - can enter lungs and cause damage. Ingestion may cause gastrointestinal irritation, nausea, vomiting and diarrhea. Harmful if swallowed. Potential for aspiration if swallowed.
Eyes	Irritating to eyes.
Skin	Irritating to skin. May be harmful in contact with skin.

Toxicology data for the components

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Decahydronaphthalene	LD50 = 4170 mg/kg (Rat)	LD50 = 5900 mg/kg (Rabbit)	LC50 = 4.08 mg/L (Rat) 4 h

Toxicologically Synergistic Products No information available

(b) skin corrosion/irritation;
Test method Category 1 C
Test species OECD 404
Observational endpoint rabbit
 Corrosive

(c) serious eye damage/irritation;
Test method Category 1 Based on available data, the classification criteria are not met
Test species OECD 405
Observation end point rabbit eye
 No eye irritation

(d) respiratory or skin sensitization;
Respiratory Based on available data, the classification criteria are not met
Skin Based on available data, the classification criteria are not met

Component	Test method	Test species	Study result
Decahydronaphthalene 91-17-8 (>95)	OECD Test Guideline 406	guinea pig	- - non-sensitising

(e) germ cell mutagenicity;
 Based on available data, the classification criteria are not met
 Not mutagenic in AMES Test

(f) carcinogenicity;
 Based on available data, the classification criteria are not met
 The table below indicates whether each agency has listed any ingredient as a carcinogen

Component	CAS No	IARC	NTP	ACGIH	OSHA	Mexico
Decahydronaphthalene	91-17-8	Not listed	Not listed	Not listed	Not listed	Not listed

(g) reproductive toxicity; Based on available data, the classification criteria are not met

(h) STOT-single exposure; Based on available data, the classification criteria are not met

(i) STOT-repeated exposure; Based on available data, the classification criteria are not met

Target Organs	None known.
(j) aspiration hazard;	Category 1 Based on available data, the classification criteria are not met
Other Adverse Effects	Tumorigenic effects have been reported in experimental animals. The toxicological properties have not been fully investigated.
Symptoms / effects, both acute and delayed	Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting. Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated. Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation.
Other Adverse Effects	Tumorigenic effects have been reported in experimental animals. The toxicological properties have not been fully investigated.
Endocrine Disrupting Properties	This product does not contain any known or suspected endocrine disruptors.

12. Ecological information

Ecotoxicity

The product contains following substances which are hazardous for the environment. Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Component	Freshwater Algae	Freshwater Fish	Microtox	Water Flea
Decahydronaphthalene	EC50: > 2.2 mg/l (Scenedesmus subspicatus)	LC50: 1.84 mg/L/48h (Oryzias latipes)	Not listed	EC50: 0.28 mg/L/48h (Daphnia magna) EC50: 0.037 mg/l/96h (Mysidopsis Bahia)

Persistence and Degradability	May persist
Bioaccumulation/ Accumulation	No information available.
Mobility	Will likely be mobile in the environment due to its water solubility. Is not likely mobile in the environment due its low water solubility.

Component	log Pow
Decahydronaphthalene	4.79

13. Disposal considerations

Waste Disposal Methods	Chemical waste generators must determine whether a discarded chemical is classified as a hazardous waste. Chemical waste generators must also consult local, regional, and national hazardous waste regulations to ensure complete and accurate classification.
-------------------------------	---

14. Transport information

DOT

UN-No	UN1147
Proper Shipping Name	DECAHYDRONAPHTHALENE
Hazard Class	3
Packing Group	III

TDG

UN-No	UN1147
Proper Shipping Name	DECAHYDRONAPHTHALENE
Hazard Class	3
Packing Group	III

IATA

UN-No	UN1147
Proper Shipping Name	DECAHYDRONAPHTHALENE
Hazard Class	3

Packing Group	III
IMDG/IMO	
UN-No	UN1147
Proper Shipping Name	DECAHYDRONAPHTHALENE
Hazard Class	3
Packing Group	III

15. Regulatory Information

United States of America Inventory

Component	CAS No	TSCA	TSCA Inventory notification - Active-Inactive	TSCA - EPA Regulatory Flags
Decahydronaphthalene	91-17-8	X	ACTIVE	-

Legend:

TSCA US EPA (TSCA) - Toxic Substances Control Act, (40 CFR Part 710)

X - Listed

'-' - Not Listed

TSCA - Per 40 CFR 751, Regulation of Certain Chemical Substances & Mixtures, Under TSCA Section 6(h) (PBT)

Not applicable

TSCA 12(b) - Notices of Export

Not applicable

International Inventories

Canada (DSL/NDL), Europe (EINECS/ELINCS/NLP), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), China (IECSC), Korea (KECL).

Component	CAS No	DSL	NDL	EINECS	PICCS	ENCS	ISHL	AICS	IECSC	KECL
Decahydronaphthalene	91-17-8	X	-	202-046-9	X	X	X	X	X	KE-02852

KECL - NIER number or KE number (<http://ncis.nier.go.kr/en/main.do>)

U.S. Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

SARA 311/312 Hazard Categories

Should this product meet EPCRA 311/312 Tier reporting criteria at 40 CFR 370, refer to Section 2 of this SDS for appropriate classifications.

CWA (Clean Water Act) Not applicable

Clean Air Act Not applicable

OSHA - Occupational Safety and Health Administration Not applicable

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material.

California Proposition 65

This product does not contain any Proposition 65 chemicals.

U.S. State Right-to-Know Regulations

Component	Massachusetts	New Jersey	Pennsylvania	Illinois	Rhode Island
Decahydronaphthalene	X	X	X	-	-

U.S. Department of Transportation

Reportable Quantity (RQ): N
 DOT Marine Pollutant N
 DOT Severe Marine Pollutant N

U.S. Department of Homeland Security

This product does not contain any DHS chemicals.

Other International Regulations

Mexico - Grade Moderate risk, Grade 2

Authorisation/Restrictions according to EU REACH

Not applicable

Component	CAS No	REACH (1907/2006) - Annex XIV - Substances Subject to Authorization	REACH (1907/2006) - Annex XVII - Restrictions on Certain Dangerous Substances	REACH Regulation (EC 1907/2006) article 59 - Candidate List of Substances of Very High Concern (SVHC)
Decahydronaphthalene	91-17-8	-	-	-

Safety, health and environmental regulations/legislation specific for the substance or mixture

Component	CAS No	OECD HPV	Persistent Organic Pollutant	Ozone Depletion Potential	Restriction of Hazardous Substances (RoHS)
Decahydronaphthalene	91-17-8	Not applicable	Not applicable	Not applicable	Not applicable

Contains component(s) that meet a 'definition' of per & poly fluoroalkyl substance (PFAS)?

Not applicable

Other International Regulations

Component	CAS No	Seveso III Directive (2012/18/EC) - Qualifying Quantities for Major Accident Notification	Seveso III Directive (2012/18/EC) - Qualifying Quantities for Safety Report Requirements	Rotterdam Convention (PIC)	Basel Convention (Hazardous Waste)
Decahydronaphthalene	91-17-8	Not applicable	Not applicable	Not applicable	Not applicable

16. Other Information

Prepared By

Health, Safety and Environmental Department
 Email: chem.techinfo@thermofisher.com
 www.thermofisher.com

Creation Date

02-Apr-2009

Revision Date

21-Dec-2025

Print Date

21-Dec-2025

Revision Summary

Updated to the U.S. Department of Labor's Occupational Safety and Health Administration

(OSHA) which published its Final Rule in the Federal Register revising the Hazard Communication Standard (HCS/HazCom), 29 CFR 1910.1200 (2024) (HCS §1910.1200, 2024), May 20, 2024, effective July 19, 2024.

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of SDS