Industrial filtration

Liqui-Cel SP 1×6 membrane contactors

Thermo Scientific™ Liqui-Cel™ Membrane Contactors provide high-performance dissolved gas control in a compact design. Utilizing hollow fiber membrane technology, Thermo Scientific membrane contactors remove dissolved gases from or add gases to compatible liquid streams in-line and without chemicals to help facilities around the world improve operating efficiency and protect product quality in many industrial processes.

Typical properties


Membrane characteristics	
Cartridge configuration	Radial flow
Liquid flow guidelines*	15 - 300 ml/min (liquid must flow on the shell side)
*Flow rates are guidelines for product selection and reflect the flow range at which the product was tested. Product may be capable of operating above listed flow range depending on liquid being degassed and user's target dissolved gas requirements.	
Membrane/potting material	Polyolefin/polyethylene
Membrane type	UP II
	Recommended for low surface tension liquids with moderate potential for solvent breakthrough
Priming volume (approximate)	
Shell side	45 ml
Operating parameters	
Pressure guidelines**	
Maximum shell side LIQUID operating temperature/pressure	
41 - 77°F (5 - 25°C)	60 psig (4.1 barg)
167°F (75°C)	15 psig (1.0 barg)
**Note: Liquid pressure should always exceed gas pressure in operation.	
Housing characteristics	
Material	Black polyethylene
Port connections	
Shell side (liquid inlet/outlet)***	• Quick disconnect compatible with CPC™ PLC12 series connectors
Lumen side (vacuum)***	• Quick disconnect compatible with CPC™ PLC12 series connectors
***Note: Use of metal connectors is not recommended.	
Seal material options for shell side wetted parts	
FFKM****	
****Only applicable to external seals. No internal seals are used.	
Weight (approximate)	
Dry	65 grams
Regulatory	
Certain Thermo Scientific™ Liqui-Cel™ SP 1x6 Membrane Contactor products are compliant with US FDA 21 CFR and other food contact regulations. Contact your Thermo Fisher Scientific representative for detailed declaration of compliance information for food contact applications.	


Not for consumer sale or use.



Note: All dimensions are nominal values. See housing drawings for additional dimensional details.

Typical properties





Notes

- Curves represent nominal values using water at 77ºF (25ºC). Characteristics may change under different operating conditions.
- Test condition O2 removal: 50 torr vacuum.
- These charts should not be used to design systems.

Intended Use: Liqui-Cel membrane contactors are intended to remove dissolved gases and bubbles from liquids or to add gases to a liquid stream. Liqui-Cel membrane contactors are for use in industrial separation applications of industrial fluids only, in accordance with the applicable product instructions, specifications, and where materials of construction are compatible. Liqui-Cel membrane contactors may further be used in the production of water for various pharmaceutical products upstream of the final water sterilization step.

Certain Liqui-Cel membrane contactors are compliant for use in Food and Beverage applications. For specific details regarding use or limitations for food contact applications please refer to the Liqui-Cel product's data sheet or contact your Thermo Fisher Scientific Inc. representative for more information.

Since there are many factors that can affect a product's use, the customer and user remain responsible for determining whether the Thermo Scientific product is suitable and appropriate for the user's specific application, including user conducting an appropriate risk assessment and evaluating the Thermo Scientific product in user's application..

Restrictions on Use: Thermo Fisher Scientific Inc. advises against the use of these Thermo Scientific products in any application other than the stated intended use(s) since other applications have not been evaluated by Thermo Fisher and may result in an unsafe or unintended condition. Do not use in any manner whereby the Thermo Scientific product, or any extractable or leachable from the Thermo Scientific product, may become part of or remain in a medical device, drug, cosmetic, supplement, infant formula; or in applications involving life-sustaining medical applications or prolonged contact with internal bodily fluids or tissues.

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by Thermo Fisher are based upon records, tests, or experience that Thermo Fisher believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with sufficient knowledge and technical skills to assess and apply their own informed judgment to the information. No license under any Thermo Fisher or third-party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond Thermo Fisher's control and uniquely within user's knowledge and control can affect the use and performance of a Thermo Scientific product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application. Failure to properly evaluate, select, and use a Thermo Scientific product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

For more information contact your Thermo Fisher Scientific sales representative or visit **thermofisher.com/industrialfiltration**

© 2026 Thermo Fisher Scientific Inc. All rights reserved. Thermo Scientific trademarks are the property of Thermo Fisher Scientific and its subsidiaries unless otherwise specified; all other trademarks are the property of their respective owners. **DTAS-15091181 GBL 0826**