

Flat sheet membrane

MICROLON 10 flat sheet membrane

Model: 10**Product type:** Flat sheet filtration membrane

Description: The Thermo Scientific™ MICROLON™ 10 Flat Sheet Membranes are made from a solution of Polyamide 6 (PA6). The membrane material is inherent hydrophilic. The asymmetrical structure of the MICROLON 10 flat sheet membrane is designed for high particle retention while still exhibiting good water permeability. Due to the different characteristics of the membrane surfaces (air and roll side) the membrane can be used in applications based on the principle of depth filtration or cake formation filtration.

Available make-up configurations: Rolls

Performance

Parameter	Value
Bubble point (in isopropyl alcohol, 23°C)	≥ 5.5 bar (≥ 79.8 psi)
Transmembrane flow (water, 23°C)	≥ 1.5 ml/(min cm ² bar) (≥ 96.1 ml/(min ft ² psi)) (≥ 0.67 ml/(min in ² psi))

Materials of construction

Hydrophilic polyamide

Physical properties

Parameter	Value
Thickness	160 ± 25 µm (6.3 ± 1 mil)

All data is based on internal Thermo Fisher Scientific testing procedures.

Intended Use: MICROLON 10 flat sheet membranes are made from polyamide 6. These are flat sheet microfiltration membrane products intended for use by customers, such as OEMs, in the manufacture of liquid microfiltration cartridges and liquid microfiltration systems for various applications, such as microelectronic semiconductors, in accordance with the product's use requirements and instructions. Since there are many factors that can affect a product's use, the customer and user remain responsible for determining whether the Thermo Scientific product is suitable and appropriate for the user's specific application, including user conducting an appropriate risk assessment and evaluating the Thermo Scientific product in user's application for safety, regulatory compliance, performance and any other requirements.

Restrictions on Use: Thermo Fisher advises against the use of these Thermo Scientific products in any application other than the stated intended use(s) since other applications have not been evaluated by Thermo Fisher and may result in an unsafe or unintended condition.

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by Thermo Fisher are based upon records, tests, or experience that Thermo Fisher believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with sufficient knowledge and technical skills to assess and apply their own informed judgment to the information. No license under any Thermo Fisher or third-party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond Thermo Fisher's control and uniquely within user's knowledge and control can affect the use and performance of a Thermo Scientific product in a particular application. Given the variety of factors that can affect the use and performance of a Thermo Scientific product, user is solely responsible for evaluating the Thermo Scientific product, conducting appropriate risk assessments, and determining whether it is fit for a particular purpose and suitable for user's method of application.

Thermo Fisher Scientific BPG GmbH

Oehder Strasse 28

42289 Wuppertal, Germany

 For more information contact your Thermo Fisher Scientific sales representative or visit thermofisher.com/membranesforoem

thermo scientific