

Medical dialysis membrane

Membrana PUREMA H capillary membrane

Product name: Thermo Scientific™ Membrana™ PUREMA™ H Capillary Membrane

Chemical composition

Polymer	Polyethersulfone
---------	------------------

Physical properties

Wall thickness	m 30 µm d ± 5 µm
Inner diameter	m 200 µm d ± 15 µm

Membrane performance characteristics

Hydraulic permeability (ultrafiltration rate for Albumin solution) (QF = 30 ml/(min x m ²))	approx. 42 ml/(h x m ² x mmHg)
Sieving coefficients (QF = 30 ml/(min x m ²))	
Cytochrome c	approx. 0.9
Albumin	approx. 0.002

Available make-up configurations

Bundles (customer specified), with P.E.T.™

All specifications are based on Thermo Fisher Scientific internal test procedures and represent average lot performance.

m = mean value
d = deviation of the mean value

Intended Use: Membrana PUREMA H capillary membranes are specialized products for OEM dialyzer and hemoconcentrator manufacturing. Membrana PUREMA H capillary membrane covers the full range for all extracorporeal renal replacement therapies, i.e., in hemodialysis, hemodiafiltration and hemofiltration. Since there are many factors that can affect a product's use, the customer and user remain responsible for determining whether the Thermo Scientific product is suitable and appropriate for the user's specific application, including user conducting an appropriate risk assessment and evaluating the Thermo Scientific product in user's application for safety, regulatory compliance, performance and any other requirements.

Restrictions on Use: Thermo Fisher advises against the use of Membrana PUREMA H capillary membrane products in any application other than the stated intended use(s), since other applications have not been evaluated by Thermo Fisher and may result in an unsafe or unintended condition.

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by Thermo Fisher are based upon records, tests, or experience that Thermo Fisher believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with sufficient knowledge and technical skills to assess and apply their own informed judgment to the information. No license under any Thermo Fisher or third-party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond Thermo Fisher's control and uniquely within user's knowledge and control can affect the use and performance of a Thermo Scientific product in a particular application. Given the variety of factors that can affect the use and performance of a Thermo Scientific product, user is solely responsible for evaluating the Thermo Scientific product, conducting appropriate risk assessments, and determining whether it is fit for a particular purpose and suitable for user's method of application.

Thermo Fisher Scientific BPG GmbH

Oehder Strasse 28

42289 Wuppertal, Germany

 For more information contact your Thermo Fisher Scientific sales representative or visit thermofisher.com/membranesforoem

thermo scientific