

Ion chromatography

Thermo Scientific Dionex suppressor


Selection guide

Description	Format		Part No.	Target applications
	Ion	Size		
Thermo Scientific™ Dionex™ NGES Next Generation Electrolytic Suppressor Designed for Thermo Scientific™ Dionex™ IC systems with electrolytic suppression capabilities	Anion Cation	4 mm 2 mm 4 mm 2 mm	060001 060003 060002 060004	General purpose self-regulating suppressor for majority of applications. Gives lowest noise for RFIC-EG hydroxide and MSA eluents for gradient applications.
Thermo Scientific™ Dionex™ CRS™ 500 Chemically Regenerated Suppressor Designed for all platforms in the chemical mode	Anion Cation	4 mm 2 mm 4 mm 2 mm	085090 085091 085092 085093	Chemically regenerated suppressor for applications requiring high levels of solvent. Required for use on systems without a suppressor power supply.
Thermo Scientific™ Dionex™ ACRS-ICE™ 500 Chemically Regenerated Suppressor for Ion Exclusion Chromatography Designed for all platforms in the chemical mode	Anion	9 mm 4 mm	084715 084714	Chemically regenerated suppressor for ion exclusion chromatography.
Thermo Scientific™ Dionex™ SC-CERS™ 500 Salt Converter Cation Electrolytically Regenerated Suppressor Designed for all platforms with CC* mode	Cation	4 mm 2 mm	083547 083549	Salt converter cation suppressor for analysis of ammonia and amines with linear calibration response.
Thermo Scientific™ Dionex™ ERD™ 500 Electrolytically Regenerated Desalter Designed for all platforms with CC* mode	Anion	4 mm 2 mm	085087 085089	Desalter for removing sodium ions from electrochemical detector effluent prior to MS detection or fraction collection.

*CC - Constant Current Mode

Thermo Scientific Dionex suppressor

Selection guide



Learn more at thermofisher.com/suppressor

For Research Use Only. Not for use in diagnostic procedures. © 2021–2023, 2026 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific and its subsidiaries unless otherwise specified. This information is presented as an example of the capabilities of Thermo Fisher Scientific products. It is not intended to encourage use of these products in any manner that might infringe the intellectual property rights of others. Specifications, terms and pricing are subject to change. Not all products are available in all countries. Please consult your local sales representative for details. **ST71644-EN 0626**

thermo scientific