

Centrifugation

Thermo Scientific S Series Centrifuges

Revolving around performance

The Thermo Scientific™ S Series General Purpose Centrifuges are designed to help provide exceptional performance, power and versatility through innovations to support efficiency across applications. The refrigerated models feature Thermo Scientific™ GreenCool™ Technology, a next-generation natural refrigerant cooling system for enhanced sustainability. These refrigerated centrifuges have a Global Warming Potential (GWP) of 3, do not contribute to ozone layer depletion, and comply with EU and US EPA F-gas regulations. Besides being less hazardous, the centrifuges use up to 6% less energy** compared to previous models. Additionally, they are manufactured in a certified zero-waste facility using 100% renewable electricity in Osterode am Harz, Germany. In the United States, we offer a recycling program that helps reduce the amount of waste sent to landfills. With advanced safety features, ergonomic design, and versatile configurations, these centrifuges turn every challenge into an opportunity.

Thermo Scientific™ features

- Intuitive user interface
- Wide range of rotors for application flexibility
- Thermo Scientific™ Auto-Lock™ Rotor Exchange
- GreenCool Technology (refrigerated models) and energy efficiency
- Improved ergonomics and user experience
- Benchtop and space-saving floor-standing models
- Thermo Scientific™ ClickSeal™ Biocontainment Lids
- IVD or general purpose models

Standard user interface | Up to 13 rotor options | Quick rotor exchange

**GREEN
COOL**
TECHNOLOGY
& SUSTAIN-
ABILITY



GLOBAL
WARMING
POTENTIAL*
3

LOWER ENERGY
CONSUMPTION
UP TO**
6%

MADE IN A
CERTIFIED
**ZERO-
WASTE**
FACILITY***

END-OF-
LIFE
RECYCLING
PROGRAM****

* Due to natural refrigerant (R290)

** Comparing maximum power consumption to previous model. Current model S4TR Centrifuge, 230V (1,750 W) and previous model: Thermo Scientific™ Sorvall™/Megafuge™ ST4R Plus Centrifuge, 230V (1,850 W).

*** Zero waste defined as less than 10% of non-hazardous waste sent to landfill, incineration or waste-to-energy

**** End of life recycling program in the United States. Visit thermofisher.com/centrifuge-recycling



Thermo Scientific™ S4T, S4TR and S4FR Centrifuges

Specifications	S4T		S4TR		S4FR		
	IVD-MD	General Use Only	IVD-MD	General Use Only	IVD-MD	General Use Only	
Swinging buckets rotors							
Maximum capacity	4 x 1,000 mL with TX-1000 rotor						
Maximum speed	6,100 rpm with H-Flex HS4 rotor						
Maximum RCF	7,196 x g with H-Flex HS4 rotor						
Fixed angle rotors							
Maximum capacity	6 x 100 mL with F15-6x100y or F10-6x100 LEX rotor						
Maximum speed	15,200 rpm with F21-48x2, Microliter 48x2 or Microliter 30x2						
Maximum RCF	25,830 x g with Microliter 30x2						
Centrifuge details							
Control system	Microprocessor						
Drive system	Direct, brushless induction low profile motor						
Accel/decel profiles	Choices of 9 accel / 10 decel rates						
Material	Front, top, sides: PC-ABS plastic painted with 2K PUR-based lacquer; metal housing: cold rolled steel with powder paint; centrifuge bowl: stainless steel; benchtop centrifuge feet: rubber/ floor-standing centrifuge feet: lockable casters						
Safety features	SMARTSpin imbalance detection, finger-pinch prevention, crash-proof construction						
Sustainability features	LCD powersave mode, greener rotor options		GreenCool technology, LCD powersave mode, greener rotor options				
Noise level ¹	<50 dB(A)		<51 dB(A)		<54 dB(A)		
Warranty	5 years limited (2 years standard warranty + 3 additional years on motor and refrigeration)						
Includes	Corrosion resistance oil (70009824), power cord, declaration of conformity (where applicable)						
Temperature range	N/A		-20°C to +40°C				
Number of compatible rotors	13						
Display details							
Display	Push button and high contrast LCD interface						
Run time	Max 9h, 59min; also with continuous and pulse modes						
Speed	Increments of 50 rpm / 50 x g						
Timer	Count down only in increments of 1 second (from 9 min 59 seconds) and in increments of 1 minute (>10 min)						
Temperature	N/A		Sample temperature in increments of 1 degree				
Program storage	Up to 6 run programs						
Programmability	Via 6 direct access buttons						
Dimensions, weight							
Dimensions HxWxD lid closed (cm)	36.2 x 56.6 x 69.0		36.1 x 74.6 x 69.5		83.5 x 56.4 x 69.6 cm		
Height lid open (cm)	86.1		86.0		135.0		
Dimensions HxWxD lid closed (inches)	14.3 x 22.3 x 27.2		14.2 x 29.4 x 27.2		32.9 x 22.2 x 27.2		
Height lid open (inches)	33.9		33.9		53.1		
Net weight (kg)	89.0		125.0 (129.0 for 100V)		155 (159 for 100V)		
Net weight (lbs)	196.2		275.6		341.8		
Gross weight (kg)	110.0		147.0 (151.0 for 100V)		188 (192 for 100V)		
Gross weight (lbs)	242.6		324.1		414.5		
Certifications and standards							
IVD/MD	✓		✓		✓		
Certifications	All models: IEC/UL/EN 61010-1, IEC/UL/EN 61010-2-020, IEC/UL/EN 61326-1, FCC part 15 Additional certification for refrigerated models: IEC/UL/EN 61010-2-011 Additional certifications for IVD-MD models: IEC/UL/EN 61010-2-101, IEC/UL/EN 61326-2-6						
Standards/ directives	ISO 14971, ISO 13485, ISO 9001 Additional directives for IVD-MD models: FDA listed, Device Class 1, EU IVDR class A						
Cleanroom compatibility	Class ISO 6 according to DIN EN ISO 14644-1				Class ISO 8 according to DIN EN ISO 14644-1		
Ordering information	S4T		S4TR		S4FR		
	IVD-MD	General Use Only	IVD-MD	General Use Only	IVD-MD	General Use Only	
	220-240V 50/60Hz (Global)	75007332*	75007333	75007357*	75007358	75007353*	75007354
	208-240V 60Hz (North America only)	75007332*	N/A	75007356*§	N/A	75007352*§	N/A
	120V 60Hz (Global)	75007331*	N/A	75007356*	N/A	75007352*	N/A
	100V 50/60Hz (Japan only)	N/A	N/A	N/A	N/A	N/A	N/A

1. Noise level measured with TX-1000 rotor at 1,000 x g/ 2,070 rpm.

*Indicates a centrifuge, rotor and/or adapter product approved for use in diagnostic applications; see user manual for details.

§ Refrigerated models are rated to be used with 120V-240V, 60Hz power sources and will include both the NEMA 5-15P (120V) and NEMA 6-15P (208V) plug heads.

Learn more at thermofisher.com/scentrifuge

thermo scientific

The intended use of the products mentioned in this brochure varies. Please refer to the product label. It is the customer's responsibility to ensure that the performance of the product is suitable for customers' specific uses or applications. © 2025 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific and its subsidiaries unless otherwise specified. **FLY-12307953 1025**